



|               |                |
|---------------|----------------|
| Product Code  | 25573          |
| Unit of sale  | 1 pc           |
| Minimum order | 1              |
| Type          | Medical device |
| Class         | II A           |

|        |     |
|--------|-----|
| UK-REP | No  |
| CH-REP | Yes |

|            |               |
|------------|---------------|
| RDM (NSIS) | 2212554       |
| CND        | V03010199     |
| EAN/UPC    | 8022386064027 |
| PARAF      | 924926518     |
| GMDN       | 17888         |

Description

VISIOFOCUS®

High accurate “non contact” thermometer that projects the temperature on the forehead.

Advantages of VisioFocus®:

- exclusive patented aiming system guarantees correct reading point and distance
- projection of the temperature on the forehead
- face button automatically adjusts forehead temperature to the environment (room) temperature for accurate result
- exclusive and patented AQCS and MQCS systems to maintain correct and constant temperature of device during long periods of use or when moving between rooms with different temperatures
- clinically tested
- totally hygienic for patients and users: no touch, no disposables
- no laser: absolutely safe for patients and users, no harm if the person eyes are open while measurement is taken
- instantaneous: gives temperature in less than 1 second
- low using cost thanks to the long battery life and speed of measurement that allows to reduce the number of thermometers and of operators necessary for a wide screening

Visiofocus® is supplied with batteries and manual (GB, FR, IT, ES)

Made in Italy.

VisioFocus® is the most advanced thermometer to precisely measure body temperature. Totally hygienic, without touching the skin, VisioFocus® reads infrared radiation naturally emitted by the surface of the skin and calculates the whole body temperature.

Technical Specifications

Forehead measuring range 34.0 /42.5°C (93.2/108.5°F)  
Measuring range (apart from forehead) 1.0/80°C (33.8/ 176°F)  
Room temperature working range 16/40°C (60.8/104°F)  
can operate also from 10 to 45°C (41-113°F), but out of the range 16-40°C (60.6-104.1°F) the accuracy is not guaranteed  
Resolution 0.1°  
Accuracy level According to ASTM E 1965-98:2016 and EN 80601-2-56  
Distance of operation: About 6 cm (2.36")  
Batteries (included) 4 AAA/LR03 type (preferably alkaline)  
Batteries life 30,000 readings or up to 3 years  
Measurement time <0.5 seconds  
Time between consecutive measurements <2 seconds