



Product Code	30725
Unit of sale	1 pc
Minimum order	1
Type	Medical device
Class	I
UK-REP	Yes
CH-REP	Yes
RDM (NSIS)	2391796
CND	Z12010702
EAN/UPC	8023279307252

Description

Alfa-flex LED - table with clamp

Three LED light sources with coinciding lenses and polycarbonate protection shield. Thanks to three independent light sources, shadows can be reduced and provide a deep cylindrical light with highly reduced heat irradiation. Each LED integrates a resistance to ensure the continuous operation of the lamp even in the rare case of a LED fault.

Design

The new design makes the lamp extremely easy to use and manoeuvre, with an additional rotation of the reflector.

Touch control

The light intensity can be adjusted through the touch button, a smooth touch of the control allows to regulate the light intensity from 4% to 100%.

Interchangeable plugs

The transformer, integrated in the plug for a lighter and smooth movements of the arm structure, is supplied with interchangeable plugs (UK, US, EU).

Flexible arm

The flexible arm ensures easier light positioning and is covered with a smooth white shrink-wrap sheath for easier cleaning and disinfection.

QR manual: GB, FR, IT, ES, PT.

Made in Italy.

Technical Specifications

Type of lighting: LED
 Consumption (Watt): 8
 Life of the bulbs (hours): > 60,000
 Light intensity at 50 cm (lux): 60,000
 Light intensity at 1 m (lux): 20,000
 Colour temperature $\pm 5\%$ at 1 m (K): 4,500
 Colour rendering index (Ra)%: 94
 Light field size at 50 cm (\varnothing mm): 150
 External \varnothing of the reflector (mm): 95
 Colour: white
 Norms: IEC 60601-1
 Marks: CE 93/42
 Weight (kg): 5
 Operating voltage V 100-240
 Operating Hz 50/60