



Product Code	30726
Unit of sale	1 pc
Minimum order	1
Type	Medical device
Class	I

UK-REP	Yes
CH-REP	Yes
RDM (NSIS)	2391771
CND	Z12010702
EAN/UPC	8023279307269

## Description

### Alfa-fix LED - trolley

Three LED light sources with coinciding lenses and polycarbonate protection shield. Thanks to three independent light sources, shadows can be reduced and provide a deep cylindrical light with highly reduced heat irradiation. Each LED integrates a resistance to ensure the continuous operation of the lamp even in the rare case of a LED fault.

### Design

The new design makes the lamp extremely easy to use and manoeuvre, with an additional rotation of the reflector.

### Touch control

The light intensity can be adjusted through the touch button, a smooth touch of the control allows to regulate the light intensity from 4% to 100%.

### Interchangeable plugs

The transformer, integrated in the plug for a lighter and smooth movements of the arm structure, is supplied with interchangeable plugs (UK, US, EU).

QR manual: GB, FR, IT, ES, PT.

Made in Italy.

## Technical Specifications

Type of lighting: LED  
 Consumption (Watt): 8  
 Life of the bulbs (hours): > 60,000  
 Light intensity at 50 cm (lux): 60,000  
 Light intensity at 1 m (lux): 20,000  
 Colour temperature  $\pm 5\%$  at 1 m (K): 4,500  
 Colour rendering index (Ra)%: 94  
 Light field size at 50 cm ( $\varnothing$  mm): 150  
 External  $\varnothing$  of the reflector (mm): 95  
 Colour: white  
 Norms: IEC 60601-1  
 Marks: CE 93/42  
 Weight (kg): 5  
 Operating voltage V 100-240  
 Operating Hz 50/60