



Product Code	33945
Unit of sale	1 pc
Minimum order	1
Type	No medical device
Class	

UK-REP	No
CH-REP	No
EAN/UPC	8023279339451

Description

CHISON ECO2 VET with 1 probe connector without probe

- ultra-compact and ultra-light weight, easy to carry
- latest LED screen technology, super bright images allow to easily view scan even outdoor
- ergonomic monitor design, 30 degree rotation, adjustable
- ultra-long battery life up to 2 hours, for outdoor scanning
- one-key to enlarge image to full screen, easy to view from distance
- streamlined workflow, easy to operate, 6-one-key to finish the cycle of diagnosis

Display modes and imaging processing
B, B/B, 4B, M, B/M, multi-frequency imaging

- Imaging processing
- compound Imaging
 - trapezoidal
 - Chroma
 - full digital beam-former
 - full screen display
 - I-image intelligent image optimization
 - THI (Tissue Harmonic Imaging)
 - SRA (Speckle Reduction Algorithm)
 - AIO (Automatic Image Optimization)

- User interface
- fold-up control panel and alphanumeric keyboard
 - back-lit keyboard for good visibility in dark room
 - interactive back-lighting
 - indicator lights identify activated keys
 - 8 TGC slides for easy adjustment
 - short cut knob for quick adjustment (hot key user- defined)
 - neat and clear keyboard layout, doctor can remember easily
 - user defined preset

- Streamlined workflow, one key to:
- select desired application with automatic preset
 - optimize the image automatically (AIO) - Make report
 - save still image and CINE loop - Measure
 - print to PC printer (laser or inkjet) or video printer (see list of compatible printers on our website)

- EASYVIEW™ Archive system
- image archive on hard disk and USB mobile storage
 - 3 USB ports
 - multiple image formats: BMP, JPG, DCM, CIN, AVI
 - cine review: auto, manual (auto review segment can be set) for 2D, M
 - cine memory capacity (256 frames/10s)

Technical Specifications

Dimension and weight: 33.5x15.5xh 35 cm (13.2"x6.1"xh 13.8"); 6 kg
Display: 12" LED, high resolution 1,024x768
Power: AC 100-240 V - 50/60 Hz

LANGUAGE - switchable by user
Software: GB, IT, FR, ES, DE, CZ, TR, CN, RU
User manual: GB, IT, FR ON REQUEST

Standard accessories

12" high resolution LED monitor - B&W
8G memory card
Hot Key
PC printer connection
3 USB port
1 ethernet port
1 video out port, 1 VGA out port
1 footswitch port
Full screen display
2 hours rechargeable lithium-ion battery: optional
Power adaptor
Standard software package
Easy View image archive system
THI