



|               |                   |
|---------------|-------------------|
| Product Code  | 35511             |
| Unit of sale  | 1 pc              |
| Minimum order | 1                 |
| Type          | No medical device |
| Class         |                   |

|         |               |
|---------|---------------|
| UK-REP  | Not required  |
| CH-REP  | Not required  |
| EAN/UPC | 8023279355116 |
| PARAF   | 903115780     |

## Description

MH Series (Mechanical timer with heater): includes 60-minute mechanical timer and continuous operation with heating capability.

### Precision cleaning power

Ultrasonic cleaning is faster and safer than any other method.

It's powerful enough to remove heavy oils and waxes, penetrating enough to deflux circuit boards, yet gentle enough to clean tiny precision assemblies.

Ultrasonic sound waves moving through a cleaning solution create an effect called cavitation, the rapid formation and implosion of microscopic bubbles.

Heat enhances the process. The deep-cleaning action of ultrasonics removes even the most stubborn dirt and contaminations.

### Branson: pioneer in ultrasonic cleaning

We have selected Branson because their cleaners incorporate years of experience in ultrasonic cleaning:

- easy to handle and safe to fill
- frequency higher than average for a deep cleaning
- less noise
- longer lifetime

All Branson cleaners are supplied with tank cover, and multilanguage manual (GB, FR, IT, ES, DE, PT, SE, NL, RU).

Recommended use with optional perforated tray.

High/low power control provides safer cleaning of delicate components. 100% power for normal or 70% for delicate applications.

## Technical Specifications

### MH series (mechanical)

- Timer: 60 minutes
- Cover
- Continuous mode
- Sweep frequency
- Heating

### BRANSON 3800

- Tank size: 290 x 150 x 150 mm
- Overall size: 397 x 317 x 377 mm
- Tank capacity: 5,7 l
- Drain and valve kit: included
- Weight: 5.4 kg
- Frequency: 40 KHz
- Power supply: 230-240 V