



|               |                |
|---------------|----------------|
| Product Code  | 43291          |
| Unit of sale  | 1 pc           |
| Minimum order | 1              |
| Type          | Medical device |
| Class         | I              |

|        |    |
|--------|----|
| UK-REP | No |
| CH-REP | No |

|            |               |
|------------|---------------|
| RDM (NSIS) | 2272298       |
| CND        | Y122127       |
| EAN/UPC    | 6933257916425 |
| PARAF      | 987474879     |
| GMDN       | 16214         |

## Description

### ELECTRIC WHEELCHAIR - 56 cm rear wheels with handrail

Electric wheelchair, for daily indoor and outdoor use.

It can be used in electric or manual mode, for easy clutchswitching.

User can move wheelchair forwards, backwards or turn around through an intelligent controller, complete with joystick to control speed and direction.

It is provided with aluminium alloy frame, hand rest, foot rest, expandable arm rest and flexible shock-proof suspension.

Removable seat and backrest cushions, battery and remote control.

Comfortable driving with ergonomic design which relieves fatigue.

Powerful: efficient energy-saving motor; high-precision gearbox; fast and stable starting. 5 speed settings.

Triple protection: electromagnetic brake and gear self-lock protection.

Stylish model: smooth light design characterized by dynamic guard plate, split fixed seat and patented arc-shaped foot rest.

Backrest folding mechanism.

Supplied with lithium battery and charger, manual (GB, IT).

## Technical Specifications

Load capacity: =100 kg  
 Enduranced mileage: =20 km  
 Maximum speed: =6 km/h  
 Battery: lithium battery, DC 24V x 18Ah  
 Motor power: 130 W  
 Power consumption: =2.5 kw x h/100 km  
 Horizontal brake performance: =1.5 m  
 Maximum safe ramp brake: =3.6 m (6°)  
 Stability: =9° (static), =6° (dynamic)  
 Noise: < 65 dB  
 Obstacle crossing height: =40 mm  
 Minimum turning radius: 1.2 m  
 Groove clearance width: 100 mm  
 Hill-holding performance: 9°  
 Size: 660 mm - open, 360 mm - closed  
 Seat width: 430 mm  
 Net weight: 29 kg  
 Protection: IPX4