



Product Code	49020
Unit of sale	1 pc
Minimum order	1
Type	Medical device
Class	I

Description

LUXIFLEX II on trolley - LED

Powerful LED light source that offers exceptional light quality. Flexible, height-adjustable and highly precise arm allows adjustment to any position. Compact head design and switch located at the base of the lamp. Class II.

Manual in: GB, FR, IT, DE, ES, PT

Made in Spain.

Technical Specifications

Consumption (Watt) 8
Life of the bulbs (hours) 50,000
Light intensity at 50 cm (lux) 25,000
Light intensity at 1 m (lux) 9,000
Colour temperature $\pm 5\%$ at 1 m (K) 4,000°
Colour rendering index (Ra)% >80
Light field size at 50 cm (\varnothing mm) 150
External \varnothing of the reflector (mm) 65
Colour white
Norms EN 60601-1-2
Marks UE 2017/745
Weight (kg) -
Operating voltage V 100/240
Operating Hz 50/60