



Product Code	49126
Unit of sale	1 pc
Minimum order	1
Type	Medical device
Class	I

UK-REP	Yes
CH-REP	Yes
RDM (NSIS)	2391814
CND	Z12010702
EAN/UPC	8023279491265

## Description

Primaled - flex light - trolley

PRIMALED COLD LIGHT LAMP WITH 9 LED LENSES

Appealing design and advanced technology.

**Design:** the round and ultra-flat shape of the light make the product ergonomic and suitable for any type of installation, from the doctor's surgery to the intensive-care unit.

**Ergo-Spring:** the movement of the articulated tubular arm is servo-assisted by a torsion spring which ensures ease of movement and stability.

**105,000 lux:** unique performance with 105,000 lux at 50 cm.

**Light intensity adjustment:** six different adjustment levels by the keys on the frontal panel.

**4,000-4,500 °K Colour temperature selection:** the comparison between the two colours (K) increases the visibility of details.

**Shadow suppression:** the radial layout of the lenses and the large-diameter lamp (195 mm) allow shadow suppression and three-dimensional lighting.

**Adjustable courtesy-light:** integrates ambient light with traditional concentrated light.

**Sterilizable removable grip:** allows best asepsis.

**Cold light:** the reduced emission of IR rays by the LEDs as well as the low power consumption allow minimum heat emission.

**60,000 hours LEDs life:** the top aluminium dome allows heat exchange, thus reducing the work temperature and considerably increasing the life cycle of the single LEDs.

**Interchangeable plugs:** transformer is integrated in the plug for a lighter and smooth movement of the arm. Supplied with interchangeable plugs (UK, US, EU).

**Fully certified:** complies with IEC 60601-1 and 60601-1-2 general medical standards and to special standard IEC 60601-2-41 93/42 EEC and 2007/47 EC and is CE marked as a Class I medical device.

**Mechanical testing and user safety:** die-cast aluminium and tubular steel structure. The articulated arm has undergone mechanical testing for 40,000 continuous movements to ensure maximum safety for the user during use.

**Light continuity:** the modular design of the LED power circuit ensures light continuity even in case of a LED fault.

The lamp lens has been designed to provide focused and deep lighting.  
Lighted field diameter is 16 cm at 0,5 m.

The following functions are controlled by the keys on the membrane keyboard:

- on/off
- selection of the 4,000°K and 4,500°K colour temperatures
- 6-level adjustment of the light intensity
- courtesy light

QR manual: GB, FR, IT, ES, PT

Made in Italy.

## Technical Specifications

LED life: >60,000 hours  
Light intensity: 105,000 lux at 50 cm, 30,000 lux at 1 m  
Colour temperature: 4,000-4,500 °K  
Colour rendering index: 95 Ra  
Illuminated field at 50 cm: Ø 150 mm  
External diameter of the reflector: 190 mm  
Temperature increase in the operating area at 1 m: 1°C  
Adjustable height with castors: 600 mm - max 1,600 mm  
Power supply: 80-240V - 50/60 Hz  
Electric absorption: 20VA  
Weight: 10 kg (trolley included)  
Light intensity adjustment: 25-100%