

# EXCLUSIVELY MANUFACTURED FOR



# GIMA

**GIMA Spa**  
Via Marconi, 1 - 20060 Gessate (MI) - Italy



**LED SpA**  
APRILIA (LT) - ITALY -

**MODEL**

**DIATERMO MB 200 D**

**CLASS**

**I CF**

**MADE IN**

**ITALY**

**DUTY CYCLE**

**ON: 10 s / OFF: 30 s**

**SN**

**395**



**CE**  
**0051**

**WARNING : NO OPERATOR SERVICEABLE PARTS INSIDE, REFER SERVICING TO QUALIFIED PERSONNEL**

ENSURE THAT THE CORRECT  
VOLTAGE IS SELECTED BEFORE  
CONNECTING TO THE MAINS  
POWER SUPPLY

115 V~ - 50/60 Hz  
350 VA - FUSE T6.3AL 250V

230 V~ - 50/60 Hz  
350 VA - FUSE T3.15AL 250V