

ENSURE THAT THE  
CORRECT VOLTAGE  
IS SELECTED  
BEFORE  
CONNECTING TO  
THE MAINS  
POWER SUPPLY








#### MAIN POWER

230 V~ - 50/60 Hz  
1000 VA

FUSE 2 X T5AL 250V

115 V~ - 50/60 Hz  
1000 VA

FUSE 2 X T10AL 250V

EXCLUSIVELY MANUFACTURED FOR			
 <b>GIMA</b> GIMA Spa - Via Marconi, 1 20060 Gessate (MI) - Italy			
FUNCTION	MAX POWER	LOAD	FREQUENCY
PURE CUT	400 W	300 $\Omega$	425 kHz
ENHANCED CUT	250 W	500 $\Omega$	425 kHz
BLEND CUT	250 W	300 $\Omega$	425 kHz
SPEEDY COAG	120 W	500 $\Omega$	425 kHz
DEEP COAG	120 W	200 $\Omega$	425 kHz
SPRAY COAG	100 W	2000 $\Omega$	425 kHz
BIPOLAR CUT	95 W	150 $\Omega$	525 kHz
BIPOLAR BLEND	90 W	150 $\Omega$	525 kHz
BIPOLAR COAG	70 W	100 $\Omega$	525 kHz
<div> <div>  LED SpA Via Salsicciatella 40 APRILIA (LT) - Italy           </div> <div>  </div> </div>			
MODEL			
DIATERMO MB 400 D			
DUTY CYCLE			
ON: 10 s			
OFF: 30 s			
CLASS			
I CF			
MADE IN ITALY			
<div> <div>  </div> <div>  </div> </div>			
<div> <div>  SN           </div> <div>  399           </div> </div>			

**WARNING : NO OPERATOR SERVICEABLE PARTS INSIDE**  
**REFER SERVICING TO QUALIFIED PERSONNEL**

