

DIATERMO MB 200 T

EXCLUSIVELY MANUFACTURED FOR: GIMA Spa Via Marconi, 1 - 20060 Gessate (MI) - Italy

model DIATERMO MB 200 T | **duty cycle** ON 10 s - OFF 30 s | **class** I CF

MONOPOLAR

CUT 200 W - 300 Ω - 360 kHz
COAG 150 W - 200 Ω - 360 kHz

BIPOLAR

CUT 200 W - 50 Ω - 360 kHz
COAG 200 W - 50 Ω - 360 kHz

WARNING: DO NOT OPEN. FOR TECHNICAL
SERVICE CONTACT QUALIFIED STAFF ONLY.

SN

645



Ensure that the correct voltage is available before
connecting to the mains power supply

100 - 240 V~
50/60 HZ
750 VA
FUSE 2X T10AL 250V



LED SpA

via Selciatella, 40
04011 Aprilia (LT) Italy
MADE IN ITALY