



100 - 240 V~ 50/60 HZ 1000 VA FUSE 2X T10AL 250V



Ensure that the correct voltage is available before connecting to the mains power supply.

EXCLUSIVE
MANUFACTURED FOR



GIMA

GIMA Spa - Via Marconi, 1
20060 Gessate (MI) - ITALY



Model **DIATERMO MB 400 T**
Duty cycle ON 10 s - OFF 30 s class I CF

MONOPOLAR

CUT	400 W - 300 Ω - 330 kHz
COAG	150 W - 300 Ω - 330 kHz

BIPOLAR

CUT	300 W - 50 Ω - 330 kHz
COAG	250 W - 50 Ω - 330 kHz



WARNING: DO NOT OPEN. FOR TECHNICAL SERVICE CONTACT QUALIFIED STAFF ONLY.



0051



LED SpA // via Selciatella, 40 // 04011 Aprilia (LT) Italy // www.led.it // MADE IN ITALY

SN

647
