

Termoforo / Heating pad**REF SS02(30*40) (GIMA 28670)**

Tensione / Voltage: 220-240V~50Hz Consumo elettricità / Power: 100 W

- Solo lavaggio a mano. • Non stirare. • Non candeggiare. • Non asciugare in asciugatrice.
- Non lavare a secco. • Non utilizzare se bagnato. • Non forare il cuscino riscaldato.
- Non utilizzare piegato o increspato. • Non utilizzare con neonati, una persona incapace o una persona insensibile al calore. • Non adatto per bambini sotto i 3 anni.
- Un'applicazione troppo lunga può causare ustioni cutanee. • Usare solo con comando staccabile SS02.
- Hand-wash only. • Do not iron. • Do not bleach. • Do not tumble dry. • Do not dry-clean.
- Do not use if wet. • Do not puncture the heated cushion. • Do not use folded or rucked.
- Do not use with infants, a helpless person or a person insensitive to heat. • Not suitable for children under 3 years. • A too long application can result in skin burns. • Used only with detachable controller SS02.



Fabbricante / Manufacturer:

Dongguan Sunbright Electric Appliance Co., Ltd.No.102, Shangdong Yiheng East Road, Qishi Town,
523455 Dongguan City, Guangdong Province, China

Made in China

Importato da / Imported by:

Gima S.p.A.

Via Marconi, 1 - 20060 Gessate (MI) Italy

gima@gimaitaly.com - export@gimaitaly.com

www.gimaitaly.com**LOT** 000001