



SERVICE
ONLY



SPEAKER
VOLUME




min

max



ENSURE THAT THE CORRECT
VOLTAGE IS SELECTED BEFORE
CONNECTING TO THE MAINS
POWER SUPPLY



EXCLUSIVELY MANUFACTURED FOR				MANUFACTURER	
 GIMA		GIMA SpA Via Marconi, 1 20060 Gessate (MI) - Italy		LED SpA FROSINONE - ITALY -	
FUNCTION	MAX POWER	LOAD	FREQUENCY	MAIN POWER	
PURE CUT	400 W	300 Ω	425 kHz	230Vac - 50/60 Hz 1000 VA FUSE 2 X T 5A	115Vac - 50/60 Hz 1000 VA FUSE 2 X T 10A
ENHANCED CUT	250 W	500 Ω	425 kHz	MODEL	
BLEND CUT	250 W	300 Ω	425 kHz		
SPEEDY COAG	120 W	500 Ω	425 kHz	DIATERMO MB400	
DEEP COAG	120 W	200 Ω	425 kHz		
SPRAY COAG	100 W	2000 Ω	425 kHz	DUTY CYCLE	CLASS
BIPOLAR CUT	120 W	150 Ω	525 kHz	inf. 10 sec / 30 sec.	I CF
BIPOLAR BLEND	100 W	150 Ω	525 kHz	  	
BIPOLAR COAG	70 W	100 Ω	525 kHz		
SERIAL NUMBER				  	
304 _____					

WARNING : NO OPERATOR SERVICEABLE PARTS INSIDE
REFER SERVICING TO QUALIFIED PERSONNEL

